







Item	Outside Dim,H*W*D	Path Length	Inside Width	VOL	UV grade Silica
	mm	mm	mm	ml	190nm-2.5um
	Standard cell with lid				
	45*12.5*3.5	1	10	0.35	SSC-01-1
	45*12.5*4.5	2		0.70	SSC-01-2
	45*12.5*7.5	5		1.7	SSC-01-3
	45*12.5*12.5	10		3.5	SSC-01-4
	45*12.5*22.5	20		7.0	SSC-01-5
	45*12.5*32.5	30		10.5	SSC-01-6
	45*12.5*42.5	40		14	SSC-01-7
	45*12.5*52.5	50		17.5	SSC-01-8
45*12.5*102.5	100	35.0		SSC-01-9	


	Standard cell with telfon stopper				
	48*12.5*7.5	5	10	1.7	SSC-01-13
	48*12.5*12.5	10		3.5	SSC-01-14
	48*12.5*22.5	20		0.7	SSC-01-15
	48*12.5*32.5	30		10.5	SSC-01-16
	48*12.5*42.5	40		14.0	SSC-01-17
	48*12.5*52.5	50		17.5	SSC-01-18
48*12.5*102.5	100	35.0		SSC-01-19	


	Micro cell with black walls and lid				
	45*12.5*7.5	5	4	0.5	SSC-01-23
	45*12.5*12.5	10		1.0	SSC-01-24
	45*12.5*22.5	20		2.0	SSC-01-25
	45*12.5*32.5	30		3.0	SSC-01-26
	45*12.5*42.5	40		4.0	SSC-01-27
45*12.5*52.5	50	5.0		SSC-01-28	


	Micro cell with black walls and telfon stopper				
	48*12.5*7.5	5	4	0.5	SSC-01-33
	48*12.5*12.5	10		1.0	SSC-01-34
	48*12.5*22.5	20		2.0	SSC-01-35
	48*12.5*32.5	30		3.0	SSC-01-36
	48*12.5*42.5	40		4.0	SSC-01-37
48*12.5*52.5	50	5.0		SSC-01-38	


	Micro cell with black walls and lid				
	45*12.5*7.5	5	2	0.25	SSC-01-43
	45*12.8*12.5	10		0.5	SSC-01-44
	45*12.5*22.5	20		1.0	SSC-01-45
	45*12.5*32.5	30		1.5	SSC-01-46
	45*12.5*42.5	40		2.0	SSC-01-47
45*12.5*52.5	50	2.5		SSC-01-48	


	Micro cell with black walls and teflon stopper				
	48*12.5*7.5	5	2	0.25	SSC-01-53
	48*12.5*12.5	10		0.5	SSC-01-54
	48*12.5*22.5	20		1.0	SSC-01-55
	48*12.5*32.5	30		1.5	SSC-01-56
	48*12.5*42.5	40		2.0	SSC-01-57
48*12.5*52.5	50	2.5		SSC-01-58	


	Self masking continuous flow through cell				
	45*12.5*7.5	5	D3	0.035	SSC-01-63
	45*12.5*12.5	10		0.07	SSC-01-64
	45*12.5*22.5	20		0.14	SSC-01-65
	45*12.5*32.5	30		0.21	SSC-01-66


	Self masking continuous flowthrough cell				
	45*12.5*7.5	5	4*12	0.24	SSC-01-73
	45*12.5*12.5	10		0.48	SSC-01-74
	45*12.5*22.5	20		1.0	SSC-01-75
45*12.5*32.5	30	1.5		SSC-01-76	


	Cylindrical cell				
	22*12.5	10	D19	2.8	SSC-01-85
	22*22.5	20		5.7	SSC-01-86
	22*52.5	50		14.0	SSC-01-87
	22*102.5	100		28.0	SSC-01-88


	Standard cell with lid and with round bottom				
	45*12.5*3.5	1	10	0.35	SSC-01-101
	45*12.5*4.5	2		1.7	SSC-01-102
	45*12.5*7.5	5		1.7	SSC-01-103
	45*12.5*12.5	10		3.5	SSC-01-104
	45*12.5*22.5	20		7.0	SSC-01-105
	45*12.5*32.5	30		10.5	SSC-01-106
	45*12.5*42.5	40		14.0	SSC-01-107
	45*12.5*52.5	50		17.5	SSC-01-108
45*12.5*102.5	100	35.5		SSC-01-109	


	Standard cell with stopper but round bottom				
	48*12.5*7.5	5	10	1.7	SSC-01-113
	48*12.5*12.5	10		3.5	SSC-01-114
	48*12.5*22.5	20		7.0	SSC-01-115
	48*12.5*32.5	30		10.5	SSC-01-116
	48*12.5*42.5	40		14.0	SSC-01-117
	48*12.5*52.5	50		17.5	SSC-01-118
	48*12.5*102.5	100		35.0	SSC-01-119


	Micro cell with black walls and with lid				
	45*12.5*7.5	5	1	0.15	SSC-01-123
	45*12.5*12.5	10		0.25	SSC-01-124
	45*12.5*22.5	20		0.5	SSC-01-125
	45*12.5*32.5	30		0.75	SSC-01-126
	45*12.5*42.5	40		1.0	SSC-01-127
	45*12.5*52.5	50		1.25	SSC-01-128


	Micro cell with black walls and with lid				
	45*12.5*7.5	5	3	1.25	SSC-01-133
	45*12.5*12.5	10		0.75	SSC-01-134
	45*12.5*22.5	20		1.5	SSC-01-135
	45*12.5*32.5	30		2.25	SSC-01-136
	45*12.5*42.5	40		3.0	SSC-01-137
	45*12.5*52.5	50		3.75	SSC-01-138


	Micro cell with black walls and with lid				
	45*12.5*7.5	5	5	0.65	SSC-01-143
	45*12.5*12.5	10		1.25	SSC-01-144
	45*12.5*22.5	20		2.5	SSC-01-145
	45*12.5*32.5	30		3.75	SSC-01-146
	45*12.5*42.5	40		5.00	SSC-01-147
	45*12.5*52.5	50		6.25	SSC-01-148


	Self masking continuous flowthrough cell				
	45*12.5*12.5	10	D1	0.01	SSC-01-154
	45*12.5*22.5	20	D1	0.016	SSC-01-155
	45*12.5*32.5	30	D1	0.025	SSC-01-156
	45*12.5*12.5	10	D1.5	0.018	SSC-01-164
	45*12.5*22.5	20	D1.5	0.036	SSC-01-165
	45*12.5*32.5	30	D1.5	0.055	SSC-01-166
	45*12.5*12.5	10	D2	0.03	SSC-01-174
	45*12.5*22.5	20	D2	0.06	SSC-01-175
45*12.5*32.5	30	D2	0.09	SSC-01-176	


	Standard fluorometer cell with lid				
	45*12.5*7.5	5	10	1.7	SSC-01-203
	45*12.5*12.5	10		3.5	SSC-01-204
	45*12.5*22.5	20		7.0	SSC-01-205
	45*12.5*32.5	30		10.5	SSC-01-206
	45*12.5*42.5	40		14.0	SSC-01-207
	45*12.5*52.5	50		17.50	SSC-01-208


	Standard fluorometer cell with teflon stopper				
	48*12.5*7.5	5	10	1.7	SSC-01-213
	48*12.5*12.5	10		3.5	SSC-01-214
	48*12.5*22.5	20		7.0	SSC-01-215
	48*12.5*32.5	30		10.50	SSC-01-216
	48*12.5*42.5	40		14.0	SSC-01-217
	48*12.5*52.5	50		17.50	SSC-01-218


	Micro fluorometer cell				
	45*12.5*12.5	10	4	1	SSC-01-224
	45 x 12.5 x 12.5	10	2	0.7	Q-524
	45 x 12.5 x 12.5	10	3	1	Q-554


	Micro cell with frosted walls and lid				
	45*12.5*7.5	5	1	0.13	SSC-01-233
	45*12.5*12.5	10		0.25	SSC-01-234
	45*12.5*22.5	20		0.5	SSC-01-235
	45*12.5*32.5	30		0.75	SSC-01-236
	45*12.5*42.5	40		1.0	SSC-01-237
	45*12.5*52.5	50		1.25	SSC-01-238


	Micro cell with frosted walls and with lid				
	45*12.5*7.5	5	2	0.25	SSC-01-243
	45*12.5*12.5	10		0.5	SSC-01-244
	45*12.5*22.5	20		1.0	SSC-01-245
	45*12.5*32.5	30		1.5	SSC-01-246
	45*12.5*42.5	40		2.0	SSC-01-247
	45*12.5*52.5	50		2.5	SSC-01-248


	Micro cell with frosted walls and with lid				
	45*12.5*7.5	5	3	0.40	SSC-01-253
	45*12.5*12.5	10		0.75	SSC-01-254
	45*12.5*22.5	20		1.50	SSC-01-255
	45*12.5*32.5	30		2.3	SSC-01-256
	45*12.5*42.5	40		3.00	SSC-01-257
	45*12.5*52.5	50		3.70	SSC-01-258


	Micro cell with frosted walls and with lid				
	45*12.5*7.5	5	4	0.5	SSC-01-263
	45*12.5*12.5	10		1.0	SSC-01-264
	45*12.5*22.5	20		2.0	SSC-01-265
	45*12.5*32.5	30		3.0	SSC-01-266
	45*12.5*42.5	40		4.0	SSC-01-267
	45*12.5*52.5	50		5.0	SSC-01-268


	Micro cell with frosted walls and with lid				
	45*12.5*7.5	5	5	0.60	SSC-01-273
	45*12.5*12.5	10		1.25	SSC-01-274
	45*12.5*22.5	20		2.5	SSC-01-275
	45*12.5*32.5	30		3.75	SSC-01-276
	45*12.5*42.5	40		5.0	SSC-01-277
	45*12.5*52.5	50		5.25	SSC-01-278

	Micro cell with frosted walls and with lid				
	45*12.5*7.5	5	2	0.25	SSC-01-283
	45*12.5*12.5	10		0.50	SSC-01-284
	45*12.5*22.5	20		1.00	SSC-01-285
	45*12.5*32.5	30		1.50	SSC-01-286
	45*12.5*42.5	40		2	SSC-01-287
	45*12.5*52.5	50		2.50	SSC-01-288

	Micro cell with frosted walls and with lid				
	45*12.5*7.5	5	4	0.50	SSC-01-293
	45*12.5*12.5	10		1.0	SSC-01-294
	45*12.5*22.5	20		2.0	SSC-01-295
	45*12.5*32.5	30		3.0	SSC-01-296
	45*12.5*42.5	40		4.0	SSC-01-297
	45*12.5*52.5	50		5.0	SSC-01-298

	Cell with lid				
	43*15*9	5	12	2.1	SSC-01-303
	43*15*14	10		4.2	SSC-01-304
	43*15*24	20		8.4	SSC-01-305
	43*15*34	30		12.6	SSC-01-306
	43*15*44	40		16.8	SSC-01-307
	43*15*54	50		21.0	SSC-01-308
	43*15*104	100		42.0	SSC-01-309

	Standard cell with stopper and level bottom				
	45*12.5*12.5	10	10	3.5	SSC-01-404

	Micro cell with frosted walls				
	50*9*9	5	5	1.0	SSC-01-424